






Mobile Filling Unit




- Single Lever Valve opens/closes flow through the unit to start/stop demineralization, no power supply required
- Pressure Vessel is built utilizing a fibre reinforced mineral plastic, providing a lightweight yet durable portable vessel
- A patented fluid flow path through the resin maximizes the capacity of the ion exchange
- A Self-contained cartridge can be replaced in seconds
- Demineralized water meets the strict water quality requirements from appliance and glycol manufacturers
- Removes all the aggressive salts such as chlorides, sulphates,
- A and nitrates which specifically attack metals like stainless steel, copper, and aluminum
- Removes scale producing ions like calcium and magnesium that damage components and block heat transfer
- A Lowers electrical conductivity, which reduces corrosion



Treats 793 USG (inlet water @ 200ppm)

The 'PUROPAL LEADER' is ideal for demineralizing fill water for closed loop hydronic systems. The quality of water, especially when mixed with anti-freeze (glycol), can have an impact on system performance. Even marginal water quality can lead to scaling, sediment deposits, and the accumulation of sludge.









$\underline{\textbf{PUROPAL} - \textbf{LEADER} \ \textbf{H}_2 \textbf{O} \ \textbf{DEMINERALIZER} \ \textbf{TECHNICAL} \ \textbf{INFORMATION}}$

APPLICATION:

The closed loop system is filled using local domestic water which has been run through the Puropal Leader. In doing so the water is demineralized, meeting fill water specifications of glycol and boiler manufacturers. It is also possible to demineralize an existing "water only" system by circulating the system water through a Puropal Leader demineralizer.

CAPACITY OF THE ION EXCHANGER:

The capacity of the ion exchange resin depends on the water hardness. The capacity for the Puropal Leader can be read off the graph to the right. For example: With a hardness of 11.7 gpg (200 ppm), Puropal Leader provides 793 USG (3,000L) of completely demineralized water.

PUROPAL LEADER Capacity: Volume Of Completely Demineralized Water 1321 gal 660 gal 793 1189 500 29.2 450 26.3 400 23.4 350 17.5 300 250 14.6 (grains 200 11.7 8.8 150 100 5.8 2.9

SPECIFICATION:

The H2O demineralizer shall be AXIOM INDUSTRIES LTD. model PUROPAL LEADER. System shall include fibre reinforced mineral plastic housing, shut off valve, conductivity and flow meter with programmable high and low conductivity limit, limit warning signal light, automatic quality monitor, total litres treated display, comes with 4xC batteries. PuroPal Leader is rated to 58 psi (399 kPa) at 140 °F (60°C). "Demineralizer Cartridge (Leader-CartHP) Purchased separately and replaced as required".

OPTIONAL ACCESSORIES:

☐ **Leader - Cart HP** -- PuroPal Leader Replacement Cartridge with HighPower resin (18L / 4.75 USG)

LIMITED WARRANTY:

The Axiom PUROPAL LEADER H₂O demineralizer is warranted against defects in materials and workmanship for one year

Project	Location
Consultant	Contractor
Unit Tag	Sales Agent